



Product Service

CERTIFICATE

No. B 077740 0028 Rev. 00

Holder of Certificate: **Watts Industries Italia S.r.l.**

Via Vienna 3
38121 Trento TN
ITALY

Certification Mark:



Product:

**Actuators
(Electric actuators)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 64105203088701

Valid until: 2026-09-13

Date, 2021-09-14

(Martin Ma)



CERTIFICATE

No. B 077740 0028 Rev. 00

Model(s): 26LC230NC2, 26LC24NC2, 26LC230NC4, 26LC24NC4

Parameters:

Rated value:	See below table
Maximum rated mechanical load:	Nominal closing force: 110N
Over voltage category:	II
Rated Impulse Withstand Voltage (Uimp):	2500 V
Degree of pollution:	2
Temperature limits of the actuator:	0°C to +50°C
Temperature limit of mounting surfaces (Ts):	0°C to +50°C
Action Type:	Modulating action
Type of movement	Linear movement
Travel time:	3min
Stroke:	2.5mm
Number of cycles of actuation (A) of each automatic action:	10000
IP protection degree:	IP64
Protection against electric shock:	Incorporated control

Model	Rated value	Remark
26LC230NC2	230VAC, Max. 1.8W 50/60Hz	Without auxiliary microswitch
26LC24NC2	24VAC, Max. 1.6W 50/60Hz	Without auxiliary microswitch
26LC230NC4	230VAC, Max. 1.8W 50/60Hz	With auxiliary microswitch
26LC24NC4	24VAC Max. 1.6W 50/60Hz	With auxiliary microswitch

Tested according to: EN 60730-2-14:2019
EN 60730-1:2016/A1:2019