



POSSIBLES COMBINATIONS (8, 10, 12 zones)



USER GUIDE



Slave 4 or 6 zones 24VAC for NC actuators (Normally Closed)



TECHNICAL CHARACTERISTICS

Operating temperature	0°C - 50°C
Protection	Clase I - IP20
Power supply	24 VAC +/- 10% 50Hz
Outputs	Zones: 6 independent zones => the maximum output power of each zones depends on thermostat connecting on this zone. The maximum current for all connected actuators is 2.5A

FUNCTION and DESCRIPTION

The **SLAVE** 6 or 4 zones are an additional connecting box which needs to be connected to a **MASTER** 24 Vac connecting box. This extension permits to add more zones in order to connect more thermostats and more actuators.

LED INDICATOR

Green: - Heating indication (water circulation on this zone)

