

MICROFLEX[®] HP

Pre-insulated piping system

Technical Data Sheet




Description

Microflex's pre-insulated piping system is composed of a thermal insulation around a carrier pipe and covered by a "closed chamber" protective UV-resistant outer casing.

Microflex HP pipe is used for the connection of external heat pumps, e.g. Air-Water Monobloc heat pumps. The intelligent design of Microflex HP combines the supply and return pipes for heating/cooling with two corrugated pipes for mains and control cables in the same outer casing. The empty corrugated pipes allow safe routing of the cables.

It provides significant advantages such as low-weight, hyper flexibility, robustness, and easy and rapid laying even over obstacles and around corners.

System accessories can be mounted without any special tools.



The Microflex HP piping system consists of four (4) integrated components and it is manufactured according to the EN 15632: 1-3 norm.

Insulating material

The insulating material used consists of cross-linked polyethylene foam. In addition to the excellent insulating properties, the closed-cell structure of the material ensures that there is only minimal water absorption. The material is CFC free.

Corrugated PE-HD double-walled casing

The UV-resistant outer casing in dark blue color is made from PE-HD according to the "closed chamber" principle, protects the inner pipe as well as the insulating material from external impacts. The ribs of the corrugated outer cover are completely closed; water ingress due to superficial damage to the outer cover is therefore impossible.


Dimensions of coils

The standard length of a coil is 100m. Tailored lengths can be cut. The coils are designed to fit standard HGV trailers and containers. For transport and storage specifications see installation manual.

Casing Ø (mm)	Coil Inner Ø (mm)	Coil Outer Ø (mm)	Coil Width (mm)
Microflex HP for heat pump			
125	1200	2100	700
160	1200	2350	850

Pre-Insulated pipes

Microflex HP



Art. No.	PE-Xa d _{out} x s (mm)	DN	Electric corrugated conduit outer/inner diameter (mm)	Outer Casing d _{out} (mm)	Weight (kg/m)	Average Thickness of Insulation (mm)	Inner Bending Radius (1) (m)
Microflex HP: PN6/SDR11 + electric conduit							
MQ12525C3225E	2 x 25 x 2.3	20-20	25/18.8 32/25	125	1,63	15	0,3
MQ12532C3225E	2 x 32 x 2.9	25-25	25/18.8 32/25	125	1,79	12	0,3
MQ16032C3225E	2 x 32 x 2.9	25-25	25/18.8 32/25	160	2,27	27	0,5
MQ16040C32E	2 x 40 x 3.7	32-32	2 x 32/25	160	2,60	15	0,6

(1) Applicable practical values without risk of pipe distortion or damage.

Details of material properties PE-Xa pipes, life expectancy, chemical resistance etc. can be found in technical datasheet Microflex system.

Accessories



Microflex dust caps

Art. No.	Ø Outer Casing	Ø Pipe
MSQ125253225	125	3x25/1x32
MSQ125323225	125	3x32/1x25
MSQ160323225	160	3x32/1x25
MSQ1604032	160	2x40/2x32



Microflex EPDM rubber end caps

Art. No.	Ø Outer Casing	Ø Pipe
MGQ1251832	125	2x25/32-1x25-1x32
MGQ1601832	160	2x25/32-1x18/20/25-1x25/28/32



Fix points

Art. No.	Thread (inch)
MFP34	3/4"MF
MFP44	1"MF
MFP54	1 1/4"MF



PE-X coupling heating 6/16 bar

Art. No.	PE-X d_out/s (mm)	Thread (inch)
MJ3413425/23	25/2.3	3/4"M
MJ3414432/29	32/2.9	1"M
MJ3415440/37	40/3.7	1 1/4"M

Pipe capacity

Microflex PEX-a for Central Heating PN 6-SDR 11

Ø Pipe/Pipe Thickness mm	Ø Outer Pipe Diameter mm	Pipe Capacity l/sec.
25/2,3	25	0,327
32/2,9	32	0,539
40/3,7	40	0,835


Determine the necessary power of the heat source

The necessary power of the heat source is calculated as a function of the required capacity and the heat loss of the network.

To calculate the heat loss one has to take into account the following factors:

- λ insulation: 0.0335 W/m.K at 10°C
0.0372 W/m.K at 40°C
- λ ground: 1 W/mK
- λ PEX-a pipe: 0,35 W/mK
- Depth of cover over top of pipe: 80cm

Heat loss graphs



For Duo

$$\Delta T = \frac{(T_v + T_r)}{2} - T_o$$

T_v : Flow temperature

T_r : Return temperature

T_o : Ground temperature

Using the above graphs the heat loss per meter can be calculated for a temperature difference (ΔT) between the pipe media and the ground temperature.

U-values

NB: The temperature value displayed above the different columns gives the temperature differential between the ground temperature and the pipe temperature (average temperature between the flow and the return).

U _{TPS} [W/(m K)]	Type	ΔT [°C]								
		10	20	30	40	50	60	70	80	90
0,426	MQ12525C3225E	4,26	8,52	12,78	17,04	21,30	25,57	29,83	34,09	38,35
0,862	MQ12532C3225E	8,62	17,24	25,86	34,48	43,10	51,72	60,33	68,95	77,57
0,391	MQ16032C3225E	3,91	7,82	11,74	15,65	19,56	23,47	27,38	31,29	35,21
0,745	MQ16040C32E	7,45	14,90	22,35	29,80	37,25	44,70	52,14	59,59	67,04

Pressure loss tables heating pipes

Pipe roughness: 0.007 mm, Water density: 0.9719 g/cm³, Water temperature: 80°C.

Heating Capacity [kW] at a given ΔT [K]							Flow [l/s]	25 x 2,3		32 x 2,9		40 x 3,7	
5	10	15	20	25	30	40		m/s	Pa/m	m/s	Pa/m	m/s	Pa/m
1,3	2,5	3,8	5,0	6,3	7,5	10,0	0,08	0,21	33	0,15	13	0,11	6
2,5	5,0	7,5	10,0	12,5	15,0	20,0	0,12	0,37	84,8	0,22	25,6	0,14	9
3,8	7,5	11,3	15,0	18,8	22,5	30,0	0,18	0,55	174,9	0,33	52,4	0,22	18,4
5,0	10,0	15,0	20,0	25,0	30,0	40,0	0,24	0,73	239,5	0,45	87,5	0,29	30,6
6,3	12,5	18,8	25,0	31,3	37,5	50,0	0,30	0,92	439,9	0,56	130,7	0,36	45,5
7,5	15,0	22,5	30,0	37,5	45,0	60,0	0,36	1,1	613,2	0,67	181,5	0,43	63,1
8,8	17,5	26,3	35,0	43,8	52,5	70,0	0,42	1,28	813,1	0,78	240	0,5	83,2
10,0	20,0	30,0	40,0	50,0	60,0	80,0	0,48	1,47	1039,3	0,89	305,8	0,58	105,9
11,3	22,5	33,8	45,0	56,3	67,5	90,0	0,55	1,68	1336	1,02	392	0,66	135,4
12,5	25,0	37,5	50,0	62,5	75,0	100,0	0,60	1,84	1569,5	1,11	459,6	0,72	158,6
13,8	27,5	41,3	55,0	68,8	82,5	110,0	0,65	1,99	1820,8	1,21	532,2	0,78	183,4
15,0	30,0	45,0	60,0	75,0	90,0	120,0	0,70	-	-	1,3	609,8	0,84	209,8
16,3	32,5	48,8	65,0	81,3	97,5	130,0	0,75	-	-	1,39	692,3	0,9	237,9
17,5	35,0	52,5	70,0	87,5	105,0	140,0	0,85	-	-	1,58	872,2	1,02	299
18,8	37,5	56,3	75,0	93,8	112,5	150,0	0,90	-	-	1,67	969,4	1,08	332
20,0	40,0	60,0	80,0	100,0	120,0	160,0	0,95	-	-	1,76	1071,5	1,14	366,6
21,3	42,5	63,8	85,0	106,3	127,5	170,0	1,00	-	-	1,85	1178,5	1,2	402,8
22,5	45,0	67,5	90,0	112,5	135,0	180,0	1,05	-	-	1,95	1290,3	1,26	440,6
23,8	47,5	71,3	95,0	118,8	142,5	190,0	1,10	-	-	2,04	1406,9	1,32	480
25,0	50,0	75,0	100,0	125,0	150,0	200,0	1,20	-	-	-	-	1,44	563,5
27,5	55,0	82,5	110,0	137,5	165,0	220,0	1,30	-	-	-	-	1,56	653,3
30,0	60,0	90,0	120,0	150,0	180,0	240,0	1,40	-	-	-	-	1,68	749,4
32,5	65,0	97,5	130,0	162,5	195,0	260,0	1,55	-	-	-	-	1,86	905,2
35,0	70,0	105,0	140,0	175,0	210,0	280,0	1,65	-	-	-	-	1,98	1016,9

Conversion: 1 watt = 0,860 kCal

The descriptions and photographs contained in this product specification sheet are supplied by way of information only and are not binding.

Watts Industries reserves the right to carry out any technical and design improvements to its products without prior notice. Warranty: All sales and contracts for sale are expressly conditioned on the buyer's assent to Watts terms and conditions found on its website at www.wattswater.eu. Watts hereby objects to any term, different from or additional to Watts terms, contained in any buyer communication in any form, unless agreed to in a writing signed by an officer of Watts.



Watts Industries Italia S.r.l.

Via Brenno, 21 • 20853 Biassono (MB) • Italy
Tel. +39 039 4986.1 • Fax +39 039 4986.222
infowattsititalia@wattswater.com • www.watts.com