


STAF, STAF-SG Series

Balancing and control valves

Technical Data Sheet



Description

STAF, STAF-SG Series flanged variable-orifice valves are designed for flow control and monitoring in climate control (heating and cooling) systems.

By connecting differential pressure gauges (**BV-SET Series**) to the piezometric connections on the valve body, these valves can be used as a diagnostic tool for monitoring system performance (flow rate, pressure and temperature).

STAF, STAF-SG



Balancing and control valve **with flanged connections** for heating and cooling systems. Shut-off and pre-setting functions; diagnosis using computerised instrument (**BV-SET Series**) on self-sealing pressure test points.

Body centre distance ISO 5752 Series 1 and EN 558-1 Series 1, flanges ISO 7005-2, EN 1092-2.

Seat seal: disc with EPDM O-ring.

Usable with water or neutral fluids, water-glycol mixtures (0-57%).

Body, STAF: Cast iron EN-GJL-25 (GG 25).

Body, STAF-SG: Ductile iron EN-GJS-400-15.

STAF DN 65÷150

Type	Part No.	DN	Kvs	Weight (Kg)
STAF	STAF65	65	85	10.0
STAF	STAF80	80	123	12.4
STAF	STAF100	100	185	17.9
STAF	STAF125	125	294	25.5
STAF	STAF150	150	400	35.0

STAF-SG DN 20÷300

Type	Part No.	DN	Kvs	Weight (Kg)
STAF-SG	STAF-SG20	20	5.7	2.3
STAF-SG	STAF-SG25	25	8.7	2.9
STAF-SG	STAF-SG32	32	14.2	4.3
STAF-SG	STAF-SG40	40	19.2	5.2
STAF-SG	STAF-SG50	50	33	6.6
STAF-SG	STAF-SG65	65	85	10.0
STAF-SG	STAF-SG80	80	123	12.4
STAF-SG	STAF-SG100	100	185	17.9
STAF-SG	STAF-SG125	125	294	25.5
STAF-SG	STAF-SG150	150	400	35.0
STAF-SG	STAF-SG200	200	765	76
STAF-SG	STAF-SG250	250	1185	122
STAF-SG	STAF-SG300	300	1450	163
*STAF-SG	STAF-SG350	350	2200	287
*STAF-SG	STAF-SG400	400	2780	391

* DN 350-400 models available to order

52189



CFC-free polyurethane insulation shells for balancing valves.

Thermal conductivity λ at 50°C: 0.028 W/mK.

Fire-resistance: Class B2 - DIN 4102.

Type	Part No.	Description
52189	52189-850	DN 50
52189	52189-865	DN 65
52189	52189-880	DN 80
52189	52189-890	DN 100
52189	52189-891	DN 125
52189	52189-892	DN 150

Technical features	
Nominal pressure	STAF: PN 16 STAF-SG: PN 25 (DN20-150), PN 16 (DN200-400)
Operating temperature	-10÷120°C
Flanges	ISO 7005-2, EN 1092-2
Body centre distance	ISO 5752 Series 1, EN 558 Series 1
No. of setpoint positions	40 (DN 20-50) 80 (DN 65-150) 120 (DN 200-250) 160 (DN 300) 200 (DN 350) 220 (DN 400)
CE Marking	CE: STAF, STAF-SG (PN 16) DN 200, STAF-SG (PN 25) DN 50-125 CE 0409: STAF-SG (PN 16) DN 250-400, STAF-SG (PN 25) DN 150.

Materials	DN 20-150	DN 200-400
Body	STAF: Cast iron EN-GJL-250 (GG 25) STAF-SG: Ductile iron EN-GJS-400-15	Ductile iron EN-GJS-400-15
Bonnet	DZR alloy	Ductile iron EN-GJS-400-15
Cone	DZR alloy	Ductile iron EN-GJS-400-15 (and gunmetal for DN350-400)
Spindle	DZR alloy	DZR alloy
Seals	EPDM	EPDM
Slip Washer	PTFE	PTFE
Bonnet Bolts	Surface treated steel	Surface treated steel
Measuring Points	DZR alloy and EPDM	DZR alloy and EPDM
Handwheel	PA (and TPE for DN65-150)	Aluminum



Application

All distribution networks, even the simplest, are made up of different branches, whose flow rates need to be defined at the design stage and must then correspond to the values calculated in the course of operation.

In an unbalanced system (Fig.1), the flow rate to the circuits nearest the pump is too high, while the flow rate to the circuits furthest from the pump is too low. The resulting temperature differences between different rooms not only detract from comfort but also increase energy consumption.

The use of thermostatic or control valves in this situation can cause noise.

The installation and correct setting of **STAF Series** balancing and control valves (Fig. 2) on boiler room manifolds, at the bottom of risers and upstream of heat production and exchange units or zones ensures correct flow distribution, thus offering immediate benefits in terms of comfort and energy saving, as well as optimising the efficiency of the control system.



Operation

The number of turns between the fully open and fully closed positions is:

- 4 turns, 40 positions (DN 20-50),
- 8 turns, 80 positions (DN 65-150),
- 12 turns, 120 positions (DN 200-250)
- 16 turns, 160 positions (DN 300)
- 20 turns, 200 positions (DN 350)
- 22 turns, 220 positions (DN 400)

To set a valve, to 2.3 turns for example, and obtain a given pressure drop (calculated either analytically or from the flow curve), proceed as follows:

1. Fully close the valve (**Fig.1**)
2. Open the valve by 2.3 turns (**Fig.2**)
3. Fully tighten the internal stem using a 3 mm hex wrench
4. The valve is now set.

To check the setting, close the valve. The indicator should show 0.0.

Now open the valve fully. The indicator should show the setpoint, in this case 2.3 (Fig. 2).

For correct valve selection and pre-setting (pressure drop), consult the flow curve, which shows the pressure drop at various setpoints and flow rates for all valve sizes.

To conduct a field check, using differential pressure gauges (**BVT-SET Series**), remove the plug and insert the needle through the test point seal; the test points are self-sealing.

Example for DN65




Fig.1 - Fully closed




Fig.2 - Valve open by 2.3 turns

Example for DN200




Fig.1 - Fully closed




Fig.2 - Valve open by 2.3

turns

Sizing

Where the pressure drop (Δp) to be balanced and the design flow are known, use the flow curve or formula shown below:

$$K_v = \frac{q}{\sqrt{\Delta p}}$$

where: $\sqrt{\Delta p}$

K_v = volumetric flow coefficient

q = flow rate in m^3/h

Δp = pressure drop (resistance) to be balanced in bar

The following can be determined from the above:

$$K_v = 0.01 \times \frac{q}{\sqrt{\Delta p}} \quad \text{if } q \text{ is expressed in l/h and } \Delta p \text{ in kPa}$$

$$K_v = 36 \times \frac{q}{\sqrt{\Delta p}} \quad \text{if } q \text{ is expressed in l/s and } \Delta p \text{ in kPa}$$

Table of K_v values at the various setpoint positions

DN 20÷50

TURN S	DN20	DN25	DN32	DN40	DN50
0.5	0.511	0.60	1.14	1.75	2.56
1.0	0.757	1.03	1.90	3.30	4.20
1.5	1.19	2.10	3.10	4.60	7.20
2.0	1.90	3.62	4.66	6.10	11.7
2.5	2.80	5.30	7.10	8.80	16.2
3.0	3.87	6.90	9.50	12.6	21.5
3.5	4.75	8.00	11.8	16.0	26.5
4.0	5.70	8.70	14.2	19.2	33.0
4.5	-	-	-	-	-
5.0	-	-	-	-	-
5.5	-	-	-	-	-
6.0	-	-	-	-	-
6.5	-	-	-	-	-
7.0	-	-	-	-	-
7.5	-	-	-	-	-
8.0	-	-	-	-	-

DN 65÷150

TURN S	DN65	DN80	DN100	DN125	DN150
0.5	1.8	2.0	2.5	5.5	6.5
1.0	3.4	4.0	6.0	10.5	12.0
1.5	4.9	6.0	9.0	15.5	22.0
2.0	6.5	8.0	11.5	21.5	40.0
2.5	9.3	11.0	16.0	27.0	65.0
3.0	16.3	14.0	26.0	36.0	100
3.5	25.6	19.5	44.0	55.0	135
4.0	35.3	29	63.0	83.0	169
4.5	44.5	41.0	80.0	114	207
5.0	52.0	55.0	98.0	141	242
5.5	60.5	65.0	115	167	279
6.0	68.0	80.0	132	197	312
6.5	73.0	92.0	145	220	340
7.0	77.0	103	159	249	367
7.5	80.5	113	175	276	391
8.0	85.0	120	190	300	420

DN 200÷400

TURNS	DN200	DN250	DN300	DN350	DN400
0.5	-	-	-	-	-
1.0	-	-	-	-	-
1.5	-	-	-	-	-
2.0	40.0	90.0	-	-	-
2.5	50.0	110	-	-	-
3.0	65.0	140	150	109	125
3.5	90.0	195	230	129	148
4.0	120	255	300	148	171
4.5	165	320	370	170	208
5.0	225	385	450	207	264
5.5	285	445	535	254	326
6.0	340	500	620	302	386
6.5	400	545	690	352	449
7.0	435	590	750	404	515
7.5	470	660	815	471	590
8.0	515	725	890	556	680
9.0	595	820	970	784	894
10	650	940	1040	957	1140
11	710	1050	1120	1100	1250
12	765	1185	1200	1260	1400
13	-	-	1320	1420	1560
14	-	-	1370	1610	1730
15	-	-	1400	1760	1940
16	-	-	1450	1870	2140
17	-	-	-	1960	2280
18	-	-	-	2040	2410
19	-	-	-	2130	2530
20	-	-	-	2200	2630
21	-	-	-	-	2710
22	-	-	-	-	2780

Balancing valves are generally selected in such a way that the desired setpoint value is reached when the valve is 75% open. This setpoint position leaves a certain margin for manoeuvre in the field.

For existing systems, it is often difficult to calculate the necessary setpoint value. To avoid undue oversizing, make sure the pressure drop, in the fully open position and at nominal flow rate, is at least 3 kPa. Similarly, when using a balancing valve on a circuit that does not require balancing a priori (e.g. the least favourable circuit), it is advisable to install a valve of the same DN as the pipe, with a setpoint position close to fully open and a pressure drop of at least 3 kPa (approximately 300 mm wg). This makes the valve, with diagnostic function, an essential tool for monitoring the actual flow rate in the field: during commissioning, you can both “open” the valve further to increase the flow rate, and measure the Δp easily with the aid of the differential pressure gauge (**BVT-SET Series**).

Charts

The flow curve enables you to determine the pressure drop of the valve, measured at the test points.

The straight line that joins the flow rate, Kv and pressure drop scales indicates the correlation between these two variables.

To obtain the setpoint positions corresponding to the different valve diameters, now draw a horizontal line from the resulting Kv.

Worked example of how to use the flow curve (DN 20-50)

Calculate the setpoint to assign to a DN 25 valve with a flow rate of 1.8m³/h and a pressure drop of 20 kPa.

Solution:

Draw a line between 1.8 m³/h and 20 kPa. The resulting Kv = 4.

From this point, draw a horizontal line that meets the DN 25 column.

The result is 2.1 turns.

Worked example of how to use the flow curve (DN 65-150)

Calculate the pre-setting value to assign to a DN 65 valve with a flow rate of 26 m³/h and a pressure drop of 25 kPa.

Solution:

Draw a line between 26 m³/h and 25 kPa.

The resulting Kv=52.

From this point, draw a horizontal line that meets the DN 65 column. The result is 5 turns.

Worked example of how to use the flow curve (DN 200-400)

Calculate the pre-setting value to assign to a DN 250 valve with a flow rate of 300 m³/h and a pressure drop of 25 kPa.

Solution:


Draw a line between 300 m³/h and 25 kPa.

The resulting Kv=600.

From this point, draw a horizontal line that meets the DN 250 column. The result is 7 turns.

Note: if any value is off the scale, you can still use the flow curves, bearing in mind that for the same pressure drop, the pairs of values (flow rate and Kv) can be read proportionally, by multiplying them by 0.1 and 10. Using the previous example again (25 kPa, Kv=52 and flow rate 26 m³/h), we can deduce that with 25 kPa we will have two pairs of values: Kv=5.2 and flow rate 2.6 m³/h, and Kv=520 and flow rate 260 m³/h.

DN 20-50




*) Recommended Zone

**) 25 dB(A)

***) 35 dB(A)

DN 65-150

DN 200-400



*) 25 db(A)
**) 35 db(A)

*) 25 db(A)
**) 35 db(A)

Installation

STAF, STAF-SG Series balancing and control valves are easy to identify: the key technical specifications, such as PN, DN, CE, flow direction arrow, material and date of casting (year, month, day) are marked on the body and handwheel.

The valves can be fitted in any position, but they are designed in such a way that their accuracy of measurement (**Fig.3**) is highest if they are fitted in the direction of flow on a straight run (**Fig.4**).

For liquids other than water (20°C), but with similar viscosity (≤ 20 cSt= $3^{\circ}E=100S.U$ SUU, i.e. the majority of water/glycol blends and water/brine solutions at room temperature), the pressure drops determined from the flow curves can be corrected by applying a correction factor based on their specific weight. At lower temperatures, the viscosity increases and the flow through the valves can become laminar. This gives rise to a deviation in the measurement of flow rate, which increases in small valves, at low settings and low differential pressures. This deviation can be corrected automatically by setting the type of fluid using the **BVT-SET Series** differential pressure gauge.

Handwheel position "0" is factory-set and must not be changed.

Use of the specific insulation shells, which are available for valves up to DN150 (**52189 Series**), provides effective insulation, reduces thermal dispersion and prevents condensation in applications involving chilled water.

The insulation shells do not conceal the indicator showing the number of turns, and are easy to remove for inspection purposes.

Handwheel position “0” is factory-set and must not be changed.

Use of the specific insulation shells, which are available for valves up to DN150 (**52189 Series**), provides effective insulation, reduces thermal dispersion and prevents condensation in applications involving chilled water.

The insulation shells do not conceal the indicator showing the number of turns, and are easy to remove for inspection purposes.




Fig. 3 - Measurement deviation *) Setpoint (% opening of valve)





Fig. 4 - Installation positions


Overall dimensions (mm)

STAF, STAF-SG



DN	D	L	H	No. of bolt holes
20	105	150	100	4
25	115	160	109	4
32	140	180	111	4
40	150	200	122	4
50	165	230	122	4
65	185	290	205	4
80	200	310	220	8
100	235	350	240	8
125	270	400	275	8
150	300	480	285	8
200	360	600	430	12
250	425	730	420	12
300	485	850	480	12
350	520	980	585	16
400	580	1100	640	16

52189



DN	L	D	C
50	390	250	252
65	450	270	272
80	480	290	292
100	520	320	322
125	570	350	352
150	660	380	382

Specification text

STAF Series

Variable-orifice balancing and control valve **STAF Series** with flanged connections DN 65-150 for heating and cooling systems. Shut-off function, pre-setting function with 80 positions on numerical indicator in the handwheel, and diagnosis using a computerised instrument (**BVT-SET Series**) on self-sealing pressure test points. Mechanical memory of the setpoint position. EN-GJL-250 (GG25) grey cast iron valve body with epoxy paint surface treatment, other parts in DZR alloy. Body centre distance ISO 5752 Series 1 and EN 558 Series 1. Flanges ISO 7005-2, EN 1092-2. Seat seal: disc with EPDM O-ring. Nominal pressure 16 bar. Operating temperature range: from -10 to 120°C. Compliant with PED 2014/68/EU.

STAF-SG Series

Variable-orifice balancing and control valve **STAF-SG Series** with flanged connections from DN 20 to DN 400 for heating and cooling systems. Shut-off function, pre-setting function with up to 80 positions on numerical indicator in the handwheel, and diagnosis using a computerised instrument (BVT-SET Series) on self-sealing pressure test points. Mechanical memory of the setpoint position. EN-GJS-400-15 ductile iron valve body with epoxy paint surface treatment, other parts in DZR alloy. Body centre distance ISO 5752 Series 1 and EN 558 Series 1. Flanges ISO 7005-2, EN 1092-2. Seat seal: disc with EPDM O-ring. Nominal pressure 25 bar up to DN150, 16 bar DN200-400. Operating temperature range: from -10 to 120°C. Compliant with PED 2014/68/EU.

The descriptions and photographs contained in this product specification sheet are supplied by way of information only and are not binding.

Watts Industries reserves the right to carry out any technical and design improvements to its products without prior notice. Warranty: All sales and contracts for sale are expressly conditioned on the buyer's assent to Watts terms and conditions found on its website at www.wattswater.eu. Watts hereby objects to any term, different from or additional to Watts terms, contained in any buyer communication in any form, unless agreed to in a writing signed by an officer of Watts.



Watts Industries Italia S.r.l.

Via Brenno, 21 • 20853 Biassono (MB) • Italy
Tel. +39 039 4986.1 • Fax +39 039 4986.222
infowattsitalia@wattswater.com • www.watts.com