



Certificate number: 2401775 (1)

Issued 05/01/2024

Expires 05/01/2029

Kiwa Regulation 4 (KUKreg4) Certification

Evaluation Guideline – Kiwa UK – EG004 – Regulation 4(1)(a)

Model number(s) – see Appendix

WATTS Industries FRANCE.

Kiwa Watertec declares that legitimate confidence exists in the products specified in this certificate and supplied by the above organisation be relied upon to comply with the Kiwa Evaluation Guideline referred above.

Which verifies the requirements of:

Regulation 4(1)a of the Water Supply (Water Fittings) Regulations 1999 England & Wales: 2009 Northern Ireland and 2014 Byelaws Scotland.

This certificate has been issued in accordance with the Kiwa regulations for product certification.

Signed on behalf of Kiwa Watertec

David Jay, Business Unit Manager – Authorised Signatory
Kiwa Watertec

Publication of this certificate is allowed.

Products are intended to be used in the UK only. For other countries, other (National) requirements will apply.

See <https://www.kiwa.com/gb/en/about-kiwa/water-products/> or the QR code below to ensure that the certificate is still valid.

CERTIFICATE

Kiwa Watertec
(A Trading Division of Kiwa Ltd)
26A Rassau Industrial Estate
Ebbw Vale
Gwent
NP23 5SD
United Kingdom
T +44 (0)1495 308185
uk.water@kiwa.com
www.kiwa.co.uk

Certificate Issued to:
WATTS Industries FRANCE
1590 avenue d'Orange CS 10101 SORGUES
84275 VEDENE cedex
France



KUKreg4

Product Certificate

Appendix to Certificate number: 2401775

The following products belong to this certificate

<p>PRODUCT DESCRIPTION Range of Type TK spring loaded, resilient trim, in-line check valve cartridges with plastic guide, stem and body and EPDM rubber 'O' -rings. For insertion into pipes or fittings with specifically dimensioned bores.</p>
<p>ATS3 – Without Production Surveillance.</p>
<p>MODEL(S) Model CO013 – DN10 W149013630 (Watts) or 149F043476 (Socla)</p> <p>Model CO015 – DN 10 149015630 (Watts) or 149F043478 (Socla)</p> <p>Model CO020 – DN 15 W149020630 (Watts) or 149F043479 (Socla)</p> <p>Model CO010 – DN 8 W149010630 (Watts) or 149F043475 (Socla)</p> <p>Model CO014 – DN10 W149014630 (Watts) or 149F043477 (Socla)</p>
<p>SIZE: See model.</p>
<p>SCOPE: Manufacturer recommended maximum working pressure 10 Bar & maximum operating temperature 65°C. Hygienic Purposes: Non-metallic materials suitable for continuous use up to 65°C.</p>
<p>MARKING Ocean, DN and model code mould on body except for Model CO020 with W, DN15 moulded on body.</p>
<p>MATERIALS Non-metallic materials assessed (BS6920) to point of discharge.</p>
<p>BACKFLOW PROTECTION NOTES N/A.</p>
<p>ADDITIONAL NOTES All water contact & exposed components satisfy opacity requirements.</p>

Extra Notes